

Power Supply

NF-S-419424-1-16A
Order Number: 70115031

Main Parameters (*)	min	typ	max	Unit
Operating Voltage	100	230	240	V AC
Operating Current		16000		mA
Operating Temperature	-20		60	°C
Storage Temperature	-40		70	°C

Technical Parameters

Lifetime	> 50,000 h
RoHS	yes

Mechanical Parameters

Size	105x100x54.5 mm
Material	aluminium
Cable length	180 mm
Wire type	H05VV-F
Housing Color	silver
Weight	658 g

(*) Over the complete operating temperature range

Features



Picture



Safety Label



Valid Revision

| 09-NOV-2021