

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- . - .

LOC

DIST

REVISIONS

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

G

H

P

LTR

DESCRIPTION

DATE

DWN

APVD


J1

REVISED PER ECO-11-020548

06FEB12

KH

DR



	2500	TAPE AND REEL	4.32[.170] MAX	INSULATION: PVC COLOR: RED BODY: COPPER PER ASTM B152, ANNEALED TIN PLATE PER ASTM B545	1-34243-1
	100	LOOSE PC/BOX	4.32[.170] MAX		8-34243-1
OBSOLETE	-	-	4.70[.185] MAX		1-34243-0
	1000	LOOSE PIECE	4.32[.170] MAX		34243
	QTY	PACKAGE TYPE	INS DIA.	MATERIAL & FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 11JAN12

KIRAN HOLAL

CHK 11JAN12

ROHDE DANIEL

APVD 11JAN12

ROHDE DANIEL

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3


00779

C-34243

SCALE 8:1

SHEET 1 OF 1

REV J1

DIMENSIONS:
mm [INCHES]TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± 0.203[.008]
4 PLC	± -
ANGLES	± 5°

MATERIAL

FINISH

-

-

TE Connectivity

NAME

WIRE SPLICE PLASTI-GRIP-BUTT
WIRE SIZE: 22-16