

## Product information

# 97 39 08

### Crimping die

For insulated and non-insulated wire ferrules

- Just one tool for the most common crimping applications
- Crimping dies changed quickly and easily without any additional tool
- Sorted and protected storage of the interchangeable dies in a round magazine
- Comfortable, powerful crimping pliers in professional quality
- Same reliable crimping results as with fixed crimping dies
- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Special quality chrome vanadium electric steel, oil-hardened
- Round magazine: glass fibre reinforced plastic



### General

Article No.	97 39 08
EAN	4003773070092
Weight	45 g
Dimensions	32 x 12 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details



Application	Wire ferrules
Capacity in square millimetres	0.25 — 6.0 mm <sup>2</sup>
Number of crimping positions	3
AWG	24 — 10

*technical change and errors excepted*