

PRODUCT-DETAILS

SP25/BL/10M

10M X SP25/BLACK CONDUIT



General Information

Extended Product Type	SP25/BL/10M
Product ID	7TCA296020R0178
EAN	5020963000195
Catalog Description	10M X SP25/BLACK CONDUIT
Long Description	Liquid Resistant, General Purpose, Highly Flexible Conduit, Nominal Conduit Size 25mm, Outside Diameter 26.0mm, Inside Diameter 21.4mm, Static Bend Radius 55mm, Reel Length 10 Meters, PVC Jacket with Galvanised Steel Core, Black

Ordering

EAN	5020963000195
Customs Tariff Number	8307106000

Dimensions

Product Net Weight	7.94 lb 3.601 kg
--------------------	---------------------

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

Additional Information

Application	Indoors / Outdoors - Light Industrial, General Purpose, Buildings
Brand / Label	Adaptaflex
Color	Black
Flexibility	High
Inside Diameter	21.4 mm
Material	Galvanized Steel Core with PVC Jacket
Nominal Size	3/4 in
Number of Batteries	0
Outside Diameter	26.0 mm
Product Name	ADAPTAFLEX
Product Type	High Flexibility Conduit
Radius	55 mm
UPC	786210259284

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	SP25/BL/10M
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	SP25/BL/10M

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5535 >> Electrical conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

