

## SylSafe EXIT

*SylSafe Exit EX C EM3 MT MS*  
0041747



### Product features

- SylSafe Exit EX C EM3 MT MS is a surface mounted emergency exit sign. Rotateable legend for wall / ceiling mounting applications. Comes with ISO7010 compliant legend pack. Arrows left, right, up, down and a blank sheet for single sided versions. EC legend pack is available as accessory. Viewing distance 26m. White housing colour. Maintained 3hr emergency operation with NiMH rechargeable battery. Recharge period 24 hours. 2.2W, IK03, IP20. Power Factor 0.6. Class II electrical construction.



## PRODUCT OVERVIEW

Product name	SylSafe Exit EX C EM3 MT MS
Technology	LED
Type	LED
Mount	Ceiling surface mounting
General application	Office, Hospitality, Retail, Museums & Galleries, Education, Logistics & Industry
ETIM Class	EC001957
Warranty	5 years
Fixture luminous flux (lm)	-
Colour temperature (K)	5700
CRI (Ra)	80
Luminous flux (emergency) (lm)	280
Electrical protection	Class II
Housing colour	White
IP rating	IP20
IK rating	IK03
Product EAN number	5410288417479

## DATA TABLE

### General data

Product name	SylSafe Exit EX C EM3 MT MS
Technology	LED
Type	LED
Mount	Ceiling surface mounting
General application	Office, Hospitality, Retail, Museums & Galleries, Education, Logistics & Industry
ETIM Class	EC001957
Warranty	5 years

### Optical data

Fixture luminous flux (lm)	-
Colour temperature (K)	5700
CRI (Ra)	80
Luminous flux (emergency) (lm)	280

## SylSafe EXIT

*SylSafe Exit EX C EM3 MT MS*

0041747

Emergency duration (h)	3
------------------------	---

### Electrical data

Mains voltage (V)	230-240V
Lamp power factor	0.6
Electrical protection	Class II
Control gear required	Yes
Drive current (mA)	18
Nominal Frequency (Hz)	50/60Hz

### Physical data

Housing colour	White
IP rating	IP20
IK rating	IK03
Nominal Product Length (mm)	308
Nominal Product Width (mm)	18
Nominal Product Height (mm)	234
Weight (kg)	0.866

### Packaging

Single packaging type	Carton
Product EAN number	5410288417479
Packaging single length / height (cm)	31.0
Packaging single width (cm)	22.6
Packaging single depth (cm)	4.4
DUN14 (outer)	05410288417479
Units per outer package	1
Packaging outer length / height (cm)	31.0
Packaging outer width (cm)	22.6
Packaging outer depth (cm)	4.4

## PHOTOMETRY

## TECHNICAL DRAWINGS

