

## Clamping heads, round version

**ORION®**

### Application:

Versatile in application, machining centres, all common axial force clamping systems on lathes and vices, measuring machines or pallet clamping.

### Execution:

- High-strength rubber/metal connection
- High retention forces
- Corrosion protection coating

|  |   |
|--|---|
| <b>Art. no.</b>                          | <b>22001 047</b>                          |
| <b>Brand</b>                             | ORION                                     |
| <b>Manufacturer Part Number</b>          | 22001047                                  |
| <b>Size</b>                              | 32  |
| <b>Design</b>                            | Without stem                              |
| <b>Profile shape</b>                     | Round with linear- and transverse grooves |
| <b>Clamping diameter</b>                 | 24 mm                                     |
| <b>Length</b>                            | 44 mm                                     |
| <b>Min./max. clamping range diameter</b> | 11-32 mm                                  |
| <b>Gross Weight</b>                      | 0.035 kg                                  |
| <b>Product Group</b>                     | 2AO                                       |



### EAN

4053625466634