

electronic pocket vernier calipers

Digital ABS point/fine callipers

Mitutoyo

Application:

For measuring, e.g. small grooves and grooves

Execution:

- Digimatic
- ABSOLUTE system for reliable measurement
- High-contrast display

Advantage:

- High resistance to water and dust (IP67 degree of protection)
- Extra finely ground measuring arms

Delivery:

Delivered in box



Art. no.	32018 077
Brand	MITUTOYO
Manufacturer Part Number	573-625-20
Min./max. length measuring range	0-150 mm
Data transmission type	DIGIMATIC
Depth gauge rod	Flat
IP protection class	IP 67
With drive wheel	Yes
Error limit	0.02 mm
Length of jaw	40 mm
Design	Metric
Digit height	9 mm
Length of cross tips	16.5 mm
Digit increment	0.01 mm
Type of locating	With locking screw
Preset function	No
With mm / inch switching	No
Length	233 mm
With automatic shut off	Yes
Battery designation	1,5 V SR44
Number of rechargeable batteries/batteries	1 PCS
Weight of rechargeable battery/battery	0.002 kg
Battery voltage	1.55 V
Type of rechargeable battery/battery	Silver oxide
Calibration Group	A
ISO	13385-1
Functions	Absolute function, Origin (Dimension preset), Automatic switch-off
Gross Weight	0.424 kg
Product Group	3MA

EAN

4946368726854