

Undercounter cabinet with CLIP-O-FLEX with pull-out system

Height 800 mm, including 6 CLIP-O-FLEX trays

CLIP-O-FLEX®

Application:

Thanks to the flexible and modular CLIP-O-FLEX system, the cabinet can be optimally designed and adapted to the individual work sequences in production, assembly, development, training and further education. Your work/storage area or your organisation system are fixed with one clip and at the same time with the highest level of horizontal and vertical flexibility.

Version:

- Solidly welded steel sheet construction
- Undercounter cabinet equipped with one door, height 540 mm and 2 drawers, front height 90 mm
- With convenient pull-out system incl. 6 CLIP-O-FLEX trays with hook-in brackets 0/40/80°

Advantage:

- CLIP-O-FLEX: flexible hook-on system with only one hooking movement
- Ergonomic workplace design thanks to different inclines and can be relocated horizontally
- Quick access to work equipment, very clear overview
- Quick retrofitting, exchange and replacement
- Best mobility, less walking required



| | |
|---|--------------------------|
| Art. no. | 50237 156 |
| Design | With pull-out system |
| Door position | Right |
| Number of cabinets 260 x 345 x 30 mm | 6 PCS |
| Load-carrying capacity per shelf board | 10 kg |
| Number of drawers | 2 PCS |
| Drawer front height | 2 x 90 mm |
| Draw width (inner dimension) | 365 mm |
| Drawer depth (inner dimension) | 294 mm |
| Pullout type | Full extension |
| Load-carrying capacity per drawer | 35 kg |
| With single pull-out safety brake | No |
| Height | 800 mm |
| Width | 474 mm |
| Depth | 405 mm |
| With doors | Yes |
| Door height | 540 mm |
| Central locking | Yes |
| Lock type | Cylinder lock |
| Material | Sheet steel |
| Cabinet colour | White aluminium RAL 9006 |
| Colour of front | Jet black RAL 9005 |
| Surface | Powder-coated |