

Compact angle grinders 125 to 150 mm



Application:

Compact angle grinder with high power reserve for effective grinding and cutting work.

Execution:

- Robust motor for daily use. Long-lasting thanks to overload protection and long carbon brush service life.
- Comprehensive user protection through rebound monitoring, restart protection, soft start and anti-vibration handgrip.
- The gear head can be rotated by 90° for a wide range of applications.
- Fast, tool-free changing of abrasives: Quick-release nut included as standard.
- High overload capability thanks to direct motor cooling.
- Industrial cable H07, 4 m length.
- Fast work progress thanks to powerful motor.



Art. no.	70374 007
Brand	FEIN
Manufacturer Part Number	72228 160000
Model	CG 17-125
Manufacturer Article Number	72228 160000
Battery included	No
Number of rechargeable batteries/batteries	0
Washer diameter	125 mm
Power input	1700 W
Power output	1010 W
Idle speed	11500 rpm
Thread dimension of spindle	M14
Weight	2.4 kg
With restart protection	Yes
With soft start	Yes
With overload protection	Yes
With electronic feedback	No
With reverse switch off	Yes
With speed control	No
With disc brake	No
With quick clamping system	No
With dead man function	No
Sound-pressure level	92 dB
Noise level	103 dB
Gross Weight	2.400 kg
Product Group	704

EAN

4014586895017