

Pneumatic belt sander/linisher CP5080-4200D24

400 W



Application:

Belt sander/linisher for industrial and production maintenance

Advantage:

- Simple replacement of sandpaper and sanding arm



Art. no.	75032 700
Model	CP5080
Max. idle speed	20000 rpm
Power output	400 W
Air consumption	5.1 l/s
Sound-pressure level	78
Connection thread	1/4 inch
Length	390 mm
Max. sanding belt width	13 mm
Weight	1.39 kg
Grinding belt length	610 mm

EAN-Code

0015451689636