

Lift lever chain hoist UNOplus

Compact, robust design

Yale

Application:

For tensioning, hoisting, pulling and tying down.

Execution:

- Compact and robust sheet steel housing
- Zinc-plated load chain in line with DIN EN 818-7 (quality class T)
- Smooth-running free-chaining feature for rapid load attachment
- 360° rotating carrying hook
- Chain end made of shatter-proof plastic
- Automatic threaded mechanical brake

Advantage:

- low tare weight
- Requires low lifting power



Art. no.	77157 080
Brand	YALE
Manufacturer Part Number	2300164
Model	UNOplus 6000
Load-carrying capacity	6000 kg
Nominal chain thickness	30 mm
Chain diameter	10 mm
Stroke force at nominal load	40 daN
Length of lever	380 mm
Stroke height per lever revolution	9 mm
Lift height	1500 mm
Min. hook spacing	690 mm
Number of load chains	2 PCS
EN standard	818-7
Gross Weight	36.000 kg
Product Group	7EE

EAN

4053981988740