

Product MD 577 G3

5 mm LED indicator
 color green

| | |
|---------------------------------------|--------------------|
| product-catalog | 5 mm LED indicator |
| color | red |
| part no | MD 577 G3 |
| forward current [mA] | 12-16 |
| forward voltage typ. [V] | 24-28 |
| wavelength [nm] | 565 |
| rec. mounting hole \varnothing [mm] | 6.35 |
| panel thickness [mm] | 1 .. 3 |
| operating temperature [°C] | -25 .. +80 |
| storage temperature [°C] | -30 .. +85 |

| | |
|-------------------------------|-----|
| chip construction | GaP |
| forward current max. [mA] | 25 |
| reverse voltage max. [V] | 4 |
| luminous intensity typ. [mcd] | 25 |

Low cost LED indicator with ribbed nylon body for easy front panel mounting

150 mm PVC leads *, AWG 26, black lead, cathode lead = blue
 * for special lead length add appendix -Lxxx (xxx length in mm) to standard P/N

note

- all dimension are in millimeter
- tolerance is ± 0.25 mm unless otherwise noted
- specifications are subject to change without notice
- version 1.0

