

# Standard carrying cases



wez BLACKLINE® carrying cases are ideal for product packaging and presentation as well as field service and repairs, etc. Standard version with flat base, comfortable handle and hinged lid. 3 standard sizes, in a range of heights.



Customised interior e.g. with pre-perforated foam interior blocks to suit your product. (See page 11 for details.)



Customised interior e.g. with Printorama® Secondo for safe transport of modules of every size. (See pages 20 – 23 for details.)



Customised e.g. with product-specific vacuum-formed insert, as sales or presentation package. Ask for details.

Part No.	External dim. mm	Internal dim. mm	
3204.390.992	300 x 200 x 063	260 x 160 x 039	
3208.397.992	300 x 200 x 110	254 x 154 x 095	
3213.397.992	300 x 200 x 154	254 x 154 x 139	
4304.397.992	400 x 300 x 063	354 x 254 x 048	
4308.397.992	400 x 300 x 110	354 x 254 x 095	
4313.397.992	400 x 300 x 154	354 x 254 x 139	
4313.387.992	400 x 300 x 154	354 x 254 x 139	<b>Light-Version</b>
4320.397.992	400 x 300 x 221	354 x 254 x 206	
4326.397.992	400 x 300 x 287	354 x 254 x 272	
6408.397.992	600 x 400 x 111	554 x 354 x 095	
6413.397.992	600 x 400 x 155	554 x 354 x 139	
6420.397.992	600 x 400 x 221	554 x 354 x 206	
6426.397.992	600 x 400 x 288	554 x 354 x 272	

# Accessories for containers and carrying cases


Useful accessories, practical additions for customising your BLACKLINE® carrying case.



*Case with reinforced lid and lock to protect your valuable products from unauthorised access. Various sizes to order.*



*Profiled foam insert for wez lid sizes 600x400 and 400x300 mm. Standard quality available from stock: pink ESD. Ask about other materials and sizes.*




*Pre-perforated antistatic pink foam blocks for customised shaping to your requirements. Max thickness 85 mm. Two sizes for either 600x400 and 400x300 mm containers.*



*Foam inserts in various sizes and materials. Standard sizes to fit 600x400 and 400x300 mm containers. Standard material is PUR conductive foam, 6 and 15 mm thick. Other sizes and materials on request.*



*Lid seal to prevent unauthorised opening of swing latches. Ensures 100% product protection.*



*Case handle 95 for mounting on BLACKLINE® containers. Simply drill 2 10 mm holes, as shown in the instructions, fit mountings from the inside and clip in handle 95—and it's finished!*

Part No.	Description	Size mm
OPTION	Reinforced lid with lock	600 x 400 / 400 x 300
2535.030.992	Profiled foam insert 1:1, pink, ESD foam, loose	252 x 352 x 30
2535.031.992	Profiled foam insert 1:1, pink, ESD foam, glued-in	252 x 352 x 30
3555.030.992	Profiled foam insert 1:1, pink, ESD foam, loose	352 x 552 x 30
3555.031.992	Profiled foam insert 1:1, pink, ESD foam, glued-in	352 x 552 x 30
2636.085.992	Pre-perforated antistatic pink foam block for 4308	260 x 360 x 85
3656.085.992	Pre-perforated antistatic pink foam block for 6408	360 x 560 x 85
2636.006.000	PUR foam insert, loose	258 x 358 x 06
2636.006.001	PUR foam insert, glued-in	258 x 358 x 06
3656.006.000	PUR foam insert, loose	358 x 558 x 06
3656.006.001	PUR foam insert, glued-in	358 x 558 x 06
2636.015.000	PUR foam insert, loose	258 x 358 x 15
2636.015.001	PUR foam insert, glued-in	258 x 358 x 15
3656.015.000	PUR foam insert, loose	358 x 558 x 15
3656.015.001	PUR foam insert, glued-in	358 x 558 x 15
9980.141.000	Lid seal, per 100	Translucent
63.9980.128.000	Case handle 95, loose	Black, conductive
63.9980.129.000	Mounting for handle 95	Black, conductive
63.9980.828.000	Case handle 95, mounted	Black, conductive