


AS-Interface control cabinet module

SmartL25 4DI C



Electrical data

Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	50

Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 4
------------------------------	-----------------------------

Inputs

Number of digital inputs	4
Input circuit of digital inputs	PNP
Sensor supply of the inputs	external (E+/E-), to PELV
Voltage supply	18...30
Max. total current rating of inputs	500
Input current High	6...10
Input current Low	0...2
Min. switching level high signal	11
Digital inputs protected against short circuits	yes

AC2254

AS-Interface control cabinet module

SmartL25 4DI C



Operating conditions					
Ambient temperature	[°C]	-25...70			
Note on ambient temperature		cRUus: -25...60 °C			
Protection		IP 20			
Tests / approvals					
EMC		EN 50295			
MTTF	[years]	485			
AS-i classification					
AS-i version		2.1			
AS-i addressing		addressing socket			
Extended addressing mode possible		yes			
AS-i profile		S-0.A.E			
AS-i I/O configuration	[hex]	0			
AS-i ID code	[hex]	A.E			
AS-i certificate		39402			
Assignment of the data bits		data bit	D0	D1	D2
		input	I-1	I-2	I-3
					I-4
Mechanical data					
Weight	[g]	142			
Type of mounting		mounting on DIN rail; string mounting possible			
Materials		PA			
Displays / operating elements					
Display		switching status		LED, yellow	
		operation		LED, green	
		errors		LED, red	
Accessories					
Accessories (optional)		COMBICON connectors			
Remarks					
Pack quantity		1 pcs.			

AC2254



AS-Interface control cabinet module

SmartL25 4DI C

Electrical connection

COMBICON:

Connection

I-	I-	E+	E-
I1	I2	I3	I4
I+	I+	I+	I+

A+	A-		

A+	AS-i +
A-	AS-i -
I+	Sensor supply +24V
I-	Sensor supply 0V
E+	external sensor supply +24V
E-	external sensor supply 0V
I1...I4	switching input sensor 1...4