


E12315



Terminating resistor for PROFIBUS DP

ProfiBus Terminat. Resistor



Application

Special feature	Free from silicone; Gold-plated contacts
Free from silicone	yes

Electrical data

Max. current load total	[A]	4; (...40 °C)
-------------------------	-----	---------------

Operating conditions

Ambient temperature	[°C]	-25...85
Protection		IP 67

Mechanical data


Weight	[g]	11.8
Dimensions	[mm]	14.5 x 14.5 x 48.5
Materials		PUR
Material nut		brass, nickel-plated

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M12, straight; Moulded body: PUR; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.6 Nm



E12315



Terminating resistor for PROFIBUS DP

ProfiBus Terminat. Resistor

Connection

