




**Actuator And Sensor Cable / PVC  
extension cable  
WKC4.5T-0.3-RSC4.5T/TEG**



- Female M12, angled, 5-pin
- Male M12, straight, 5-pin
- Sheath material: PVC
- Sheath color: grey
- Resistant to chemicals and oils
- Flame retardant
- Resistant to acids and alkaline solutions
- Resistant to microbes and hydrolysis
- LABS free
- Approval: cULus
- RoHS conform
- Protection class IP67
- Cable length: 0.3 m

**Type designation** WKC4.5T-0.3-RSC4.5T/TEG  
**Ident no.** 6629866

**Cable Cross-section**



**Connector A side**  
 Number of pins: Female connector, M12 1, Angled 5  
 Contacts: Brass, CuZn, Gold-plated  
 Contact carriers: Plastic, TPU, Black  
 Grip: Plastic, TPU, Black  
 Coupling nut/screw: Brass, CuZn, Nickel-plated  
 Seal: Plastic, FPM/FKM  
 Protection class: IP67, A + B side screwed together  
 Mechanical lifespan: > 100 Mating cycles  
 Pollution degree: 3  
 Tightening torque: 0.8 ... 1 Nm (observe max. torque of counter piece!)

**Connector B side**  
 Number of pins: Connector, M12 x 1, Straight 5 pins  
 Contacts: brass, CuZn, Gold-plated  
 Contact carriers: Plastic, TPU, Black  
 Grip: plastic, TPU, black  
 Coupling nut/screw: Brass, CuZn, Nickel-plated  
 Protection class: IP67, only in screwed state  
 Mechanical lifespan: > 100 Mating cycles  
 Pollution degree: 3  
 Tightening torque: 0.8 ... 1 Nm (observe max. torque of counter piece!)

**General data**  
 Cable diameter: 5.5 ± 0.20mm  
 Cable length: 0.3 m  
 Cable quality: PVC  
 Cable color: Gray  
 Core insulation: PVC  
 Core colors: BN, WH, BU, BK, GY  
 Core cross-section: 5x0.34mm<sup>2</sup>  
 Arrangement of strands: 42x0.1 mm

**Electrical features at +20 °C**  
 Current: 4 A  
 Rated voltage: 60 V  
 Insulation resistance: > 30.5 MΩ/km  
 Test voltage: 2000 V  
 Forward resistance: max. 57 Ω/km

**General information**

Drawing depicts design version including hexagon coupling nut (Production date after CW11/2016).

**Circuit Diagram**



**Actuator And Sensor Cable / PVC  
extension cable  
WKC4.5T-0.3-RSC4.5T/TEG****Mechanical and chemical properties**

---


Bending radius (stationary laying)	> 5 x Ø
Bending radius (flexible use)	> 10 x Ø
Ambient temperature	
Stationary	-40...+105°C
In motion	0...+80°C

**Actuator And Sensor Cable / PVC  
extension cable  
WKC4.5T-0.3-RSC4.5T/TEG**

**TURCK**

Industrial  
Automation

**Accessories**

Type code	Ident no.	Description	
Torque-Wrench-Set-AS	6936170	Torque wrench set; handles with adjustable torque 0.4-1.0 Nm, torque wrench for M8 (SW9), fork wrench for M12 (SW 14)	
BLANK-LABEL-FOR-CORDESETS-TEL-TXL	6936206	Label for TEL and TXL cables, length: 18 mm, height: 4 mm, material: polycarbonate (PC), color: white, halogen-free and flame-retardant	