




Datenblatt - Fiche technique - Data sheet

**11.04.5202**




ROLINE VGA-Kabel HD15 ST - ST, 2,0m

ROLINE Câble HD15 M/HD15 M, 2,0m

ROLINE HQ VGA Cable, HD15, M/M, 2 m

# ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE



**NOTE:**

- CABLE:UL-2919 28AWG(7/0.127 T.C)\*3COAX(75 OHMS)  
+28AWG(7/0.127 T.C)\*7C+AL/MY+D.W+BRAID(82%)  
PVC JACKET, COLOR:BLACK(NK-K01) OD:∅ 8.5±0.15mm, (C2919311-1)
- CONNECTOR:  
P1&P2:HDB15P MALE, GOLD FLASH CONTACT, NICKEL PLATED SHELL  
(THE 9TH PIN UNLOAD)
- SHIELD:COPPER-FOIL 360°SOLDERED TO CONNECTOR SHELL & CABLE BRAID
- HOOD:MOLDED TYPE, PVC 45P, COLOR:BLACK(NK-K01)
- ELECTRICAL TEST: <1>. 100% OPEN SHORT & MIS WIRE TEST  
<2>. CONTACT RESISTANCE 3 Ohms MAX  
<3>. INSULATION RESISTANCE 10M Ohms MIN
- PACKING:EACH PC / POLYBAG + BIG HEADER CARD + BAR CODE LABEL.

**PIN OUT**



11.04.5206	6000±50	10	7611990111589
11.04.5203	3000±30	20	7611990111572
11.04.5202	2000±30	20	7611990111565
P/N	L±T(mm)	PCS/CTN	BAR CODE NO.

Tolerance	Inch	M/M
.X	.015	.30
.XX	.010	.10
.XXX	.005	.05

**Rotronic Co., LTD.**

ROLINE HQ VGA Cable, HD15 M - HD15 M

Draw  
FANNIE 11/17/09'  
Chck  
Engr

Scale NONE Units m/m Third Angle Projection  
Dwg No. 120-3205 REV:A Sheet 1/1