

ROLINE Cat.6 S/FTP (PiMF) Cable, Stranded, AWG23, 300 m

Product No.	21.15.0892
Manufacturer	ROLINE
Manufacturer No.	21.15.0892
EAN (single piece)	7611990110353

roline[®]
Designed for Professionals



Cat.6

- Structured building wiring
- Impedance: 100 Ohm
- Colour: Grey
- Construction:
 - 8 lines, stranded copper wire, AWG26
 - pairs shielded with aluminium foil
 - complete shielding in tinned copper braid

For a structured cabling system we recommend to use the following components:

- ROLINE Cat.6 S/FTP Cable, Solid Wire, AWG23: 21.15.0890 (100 m), 21.15.0891 (300 m)
- ROLINE Cat.6 Flush Mount Wall Jack, shielded: 25.16.8492 (white), 25.16.8493 (ivory)
- ROLINE Cat.6 Surface Mount Wall Jack, shielded: 25.16.8392 (white), 25.16.8393 (ivory)
- ROLINE Cat.6 19" Patch Panel, 24 Ports, shielded: 26.11.0351 (light grey), 26.11.0361 (black)
- ROLINE Cat.6 S/FTP Patch Cord, grey, 5 m: 21.15.0835

The accredited German laboratory GHMT has tested and certified this product combination, in a Channel of 100 meters, as being compliant to Class E specifications; certificate no. z2365b-10-E (with flush mount)/z2364b-10-E (with surface mount).

Technical specifications	
Manufacturer	ROLINE
Product group	Twisted Pair Cable
Product type	installation cable
Colour	grey
Length	300 m
Shield type	SFTP
Transfer quality	Cat6 / Class E
Impedance	100 Ohm
Quantity of wires	8
Conductor cross section (AWG)	AWG 26
Conductor type	Wire
Cable LSOH	No

Material (external cable PVC
mantle)