LQW04AN36NH20#

"#" indicates a package specification code.


















< List of part numbers with package codes > LQW04AN36NH20D , LQW04AN36NH20B

Shape



References

	Packaging code	Specifications	Minimum quantity
	D	φ180mm Paper taping	10000
	В	Packing in bulk	500

Mass (Typ.)		
1 piece		0.0003g

Specifications

Inductance	36nH ±3%
Inductance test frequency	100MHz
Rated current (Itemp) (Based on Temperature rise)	155mA
Max. of DC resistance	1.4Ω
Q (min.)	19
Q test frequency	250MHz
Self resonance frequency (min.)	3.8GHz
Operating temperature range (Self-temperature rise is included)	-55 to 125°C
Series	LQW04AN_20

1 of 1



^{1.} This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



^{2.} This datasheet has only typical specifications because there is no space for detailed specifications