

BLINDNIETE



FLACHRUNDKOPF (~ DIN EN ISO 15977)

BLIND RIVETS

DOMED HEAD (~ DIN EN ISO 15977)

RIVETS AVEUGLES


TÊTE PLATE (~ DIN EN ISO 15977)









Aluminium AIMG 3,5
Aluminium AIMG 3,5
Aluminium AIMG 3,5


Stahl verzinkt
Steel zinc plated
Acier zingué







Ø 5,0 mm

D1 = 5,0 + 0,08 / - 0,15 mm
D2 = 9,5 + 0 / - 1,0 mm
k = 1,1 + / - 0,3 mm
d = 2,7 mm
P ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 5,1 mm

	F-Max		CODE				
5,0 x 6,0 mm	11,4 mm	0,5 - 2,5 mm	70701 50600	1820 N	2100 N	500	5000
5,0 x 8,0 mm	13,4 mm	2,5 - 4,5 mm	70701 50800			500	5000
5,0 x 10,0 mm	15,4 mm	4,5 - 6,0 mm	70701 50100			500	5000
5,0 x 12,0 mm	17,4 mm	6,0 - 8,0 mm	70701 50120			500	5000
5,0 x 14,0 mm	19,4 mm	8,0 - 10,0 mm	70701 50140			500	5000
5,0 x 16,0 mm	21,4 mm	10,0 - 12,0 mm	70701 50160			500	5000
5,0 x 18,0 mm	23,4 mm	12,0 - 14,0 mm	70701 50180			500	5000
5,0 x 20,0 mm	25,4 mm	14,0 - 16,0 mm	70701 50200			250	2500
5,0 x 25,0 mm	30,4 mm	17,0 - 20,0 mm	70701 50250			250	2500
5,0 x 27,0 mm	32,4 mm	20,0 - 23,0 mm	70701 50270			250	2500
5,0 x 30,0 mm	35,4 mm	23,0 - 25,0 mm	70701 50300	1400 N	1800 N	250	2500
5,0 x 35,0 mm	40,4 mm	25,0 - 30,0 mm	70701 50350			250	2500
5,0 x 40,0 mm	45,4 mm	30,0 - 35,0 mm	70701 50400			100	1000
5,0 x 45,0 mm	50,4 mm	35,0 - 40,0 mm	70701 50450			100	1000
5,0 x 50,0 mm	55,4 mm	40,0 - 45,0 mm	70701 50500			100	1000
5,0 x 55,0 mm	60,4 mm	45,0 - 50,0 mm	70701 50550			100	1000
5,0 x 60,0 mm	65,4 mm	50,0 - 55,0 mm	70701 50601			100	1000
5,0 x 65,0 mm	70,4 mm	55,0 - 60,0 mm	70701 50650			100	1000

Ø 6,0 mm

D1 = 6,0 + 0,08 / - 0,15 mm
D2 = 12,0 + 0 / - 1,5 mm
k = 1,5 + / - 0,4 mm
d = 3,6 mm
P ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 6,1 mm

	F-Max		CODE				
6,0 x 8,0 mm	13,9 mm	2,0 - 4,0 mm	70701 60800	2400 N	3400 N	250	2500
6,0 x 10,0 mm	15,9 mm	4,0 - 6,0 mm	70701 60100			250	2500
6,0 x 12,0 mm	17,9 mm	6,0 - 8,0 mm	70701 60120			250	2500
6,0 x 14,0 mm	19,9 mm	7,0 - 9,0 mm	70701 60140			250	2500
6,0 x 16,0 mm	21,9 mm	9,0 - 11,0 mm	70701 60160			250	2500
6,0 x 18,0 mm	23,9 mm	11,0 - 13,0 mm	70701 60180			250	2500
6,0 x 20,0 mm	25,9 mm	12,0 - 15,0 mm	70701 60200			250	2500
6,0 x 22,0 mm	27,9 mm	13,0 - 17,0 mm	70701 60220			250	2500
6,0 x 25,0 mm	30,9 mm	16,0 - 19,0 mm	70701 60250			250	2500
6,0 x 26,0 mm	31,9 mm	17,0 - 20,0 mm	70701 60260			250	2500
6,0 x 30,0 mm	35,9 mm	20,0 - 24,0 mm	70701 60300	250	2500		