

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5013340100](#)
Status: **Active**
Overview: Pico-Clasp Wire-to-Board Connectors
Description: Pico-Clasp 1.00mm Pitch Wire-to-Board Crimp Terminal, 28-32 AWG, Tin Plating, Loose

Documents:

3D Model	Product Specification PS-501940-001-001 (PDF)
Drawing (PDF)	Packaging Specification SPK-501334-001-001 (PDF)
Product Specification PS-501331-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	501334
Application	Signal, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Pico-Clasp Wire-to-Board Connectors
Packaging Alternative	501334-0000 (Reel)
Product Name	Pico-Clasp
UPC	822348531097

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	8.600/mg
Packaging Type	Bag
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.80mm max.
Wire Size AWG	28, 30, 32
Wire Size mm ²	N/A


Electrical

Current - Maximum per Contact	1.0A
-------------------------------	------

Material Info

Reference - Drawing Numbers

Crimp Specification	CS-501193-001-001
Packaging Specification	SPK-501334-001-001
Product Specification	PS-501331-001-001, PS-501940-001-001
Sales Drawing	5013340000-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[501334 Series](#)

Mates With

[501331 PCB Header](#)

Use With

[501330 Crimp Housing](#)