

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0782271001](#)
Status: **Active**
Overview: [GbX I-Trac Backplane Connector System](#)
Description: [GbX I-Trac Vertical Receptacle, Power Module, 2 Blades, 40 Amps, Lead-Free](#)

Documents:

3D Model	Packaging Specification PK-78227-001 (PDF)
Drawing (PDF)	Packaging Specification PK-78227-002 (PDF)
Product Specification PS-78231-006-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Backplane Connectors
Series	78227
Application	Backplane, Midplane
Component Type	Power Receptacle
Overview	GbX I-Trac Backplane Connector System
Product Name	GbX I-Trac
UPC	822350961400

Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Circuits Detail	40 Amps (20/Split Blade)
Color - Resin	Black
Durability (mating cycles max)	100
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.585/g
Number of Columns	1
Number of Pairs	4
Number of Rows	2
Orientation	Vertical
PC Tail Length	2.41mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.00mm, 7.40mm
Pitch - Termination Interface	2.00mm, 7.40mm
Polarized to PCB	No
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-20° to +85°C
Termination Interface: Style	Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact	40.0A
-------------------------------	-------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[78227](#) Series

Mates With

[78229](#) GbX I-Trac Right Angle Header with
Right Hold Down

Use With

[76015](#) GbX I-Trac Vertical, 7 Row Header
Module

Data Rate	12.0 Gbps
Shield Type	N/A
Shielded	No
Voltage - Maximum	250V DC

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info**Reference - Drawing Numbers**

Packaging Specification	PK-78227-001, PK-78227-002
Product Specification	PS-78231-006-001
Sales Drawing	SD-78227-011

This document was generated on 05/20/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION