


CUSTOMER	MCM
PRODUCT NO.	24-120** series




SIDE:A

SIDE:B

CUSTOMER P/N	24-12050	24-12051	24-12052	24-12053	24-12054	24-12055
L±T(MM)	460±10	920±10	1830±20	3660±20	7620±40	15240±100
Tie(MM)	60MM	80MM	110MM	130MM	160MM	PE film 600MM
Winding ø(MM)	100±15		120±15		140±15	170±15
MCM Nylon bag	200*270*0.06MM					270*350*0.06MM

NOTE:

(1).Cable Spec: SLV Series AUDIO/VIDEO Interconnect Cable[(10/0.12BC)*2C(WHITE/RED)+S(32/0.10BC)]
 Jacket Material:PVC OD:4.0mm
 Cable Colour: Cool Grey 11C
 Cable Printing:SLV Series AUDIO/VIDEO Interconnect Cable www.stellarlabs.com




- 24-12051 3FT Bar Code:8 82459 00865 9
- 24-12052 6FT Bar Code:8 82459 00866 6
- 24-12053 12FT Bar Code:8 82459 00867 3
- 24-12054 25FT Bar Code:8 82459 00868 0
- 24-12055 50FT Bar Code:8 82459 00869 7

(2).Connector A: 3.5mm Male Solder Type
 INSULATION:Black
 CONTACTS:Nickel Plated

(3).Connector B: 3.5mm Male Solder Type
 INSULATION:Black
 CONTACTS:Nickel Plated

<u>SIDE:A</u>		<u>SIDE:B</u>	
ø3.5 PLUG		ø3.5 PLUG	
1	WHITE	1	
2	RED	2	
3	F	3	



(4).Over Mold: PVC-45P-Cool Grey 11C
 (5).Parameter Settings: CT-8681FA

PIN OUT:(5)

PACKING :(8)

- 1. Conductive Resistance:1.0Ω
- 2. Insulative Resistance:5MΩ (Min.)
- 3. Hi-Pot:300V/AC、DC , 1.5mA/I , 50Hz , 0.03s

(6).100% OPEN, SHORT&MISWIRE TEST;
 (7).ALL MATERIALS MUST BE IN LINE WITH RoHS.
 (8).Packing:Nylon bag+label

GENERAL TOLERANCES (UNLESS SPECIFIED)		MCM Electronics www.mcmelectronics.com					
LENGTH: X. ±1 .X ±0.2 .XX ±0.10 ANGLE: X° . ±1° .X° ±0° 30'						UNIT:mm	REV:0/A
DRAWING	XIAODENG	2014/04/04	S. P. NO.	HT-5762	DWG. NO.		
CHECK			P. O. NO.		PAGE		1/1
APPROVE			SIZE				

0	NEW	2014/04/04
REV	DESCRIPTION	DATE