






REV	DESCRIPTION	SIGNATURE	DATE
AO	ORIGIN	Flynn	2020.07.09
A1	Add the size	Flynn	2021.04.10

TABLE A



NOTES:
7680*4320@60Hz
Support 100M

ITEM	SPECIFICATIONS	Q' TY	UNIT
1 2	QR Code Label	1	PCS
1 1	Screwer	4	PCS
1 0	Spring Lock	2	PCS
9	SR Black	2	PCS
8	DP A male metal shell(bottom)black(Display)	1	PCS
7	DP A male metal shell(bottom)black(Source)	1	PCS
6	DP A male metal shell push botton black	2	PCS
5	DP A male metal shell(upon)black	2	PCS
4	DP A PCBA (Display)	1	PCS
3	DP A PCBA (Source)	1	PCS
2	DP A male , gold plated	2	PCS
1	DP AOC (4 fiber +8 copper) black TPU OD5.8MM	TABLE A	m m

TOLERANCES UNLESS OTHERWISE STATED	
X.	= ± 1
X.X	= ± 0.25
X.XX	= ± 0.1
TOOLING DECIMALS ANGLES	
X.	±0.3 ± 1°
X.X	±0.2 ± 0.5°
X.XX	±0.1 ± 0.5°

TYPE: DP 1.4 Armoured Active Optical Cable		
DRAW: Flynn		
CKD:	CUSTOMER:	UNIT:mm
APP:	DWG NO:B0200709-0033	REV:A1
SHELL:1/1		DATE:2021.04.10