

Electronic 3-point internal micrometer

IP67, carbide-tipped measuring surfaces



Application:

For measuring through holes and blind bores (from diameter 12.5 mm) and short centring shoulders.

Execution:

- Self-centring and self-aligning
- Carbide measuring faces
- Friction coupling for consistent, repeatable measuring force
- ON/OFF
- Zero setting at any position
- mm/inch switch-over
- Max./min. value memory
- HOLD function
- Preset function
- Tolerance function

Delivery:

Single device with battery (1 x 3 V lithium type CR 2032) and calibration certificate in a case



Art. no.	31917 035
Brand	SYLVAC
Manufacturer Part Number	950.6018
Min./max. length measuring range	35-50 mm
Measuring depth	80 mm
Data transmission type	Bluetooth/Proximity
Digit increment	0.001 mm
IP protection class	IP 67
Measuring spindle increments	0.5 mm
Error limit	4 µm
Display	Digital
Number of rechargeable batteries/batteries	1 PCS
Battery designation	3V CR2032 Lithium
DIN	863
Gross Weight	1.132 kg
Product Group	317

EAN

7640125715842