

## KHE 2660 QUICK combination hammer

850 W

**metabo**

### Application:

for hammer drilling, non-impact drilling and chipping

### Execution:

- Metabo S-automatic safety clutch
- aluminium alloy housing
- Metabo Quick: Quick-change between the hammer chuck suitable for tools with SDS-plus insertion ends and quick-action drill chuck
- cable-protecting ball joint
- convenient lockable switch for continuous work
- Vario (V) electronics for working with speeds suitable for the material

### Delivery:

hammer chuck suitable for tools with SDS-plus shanks, quick-action drill chuck for tools with cylindrical shanks, rubberised additional handle, drilling depth stop, in plastic case



<b>Art. no.</b>	<b>70171 065</b>
<b>Brand</b>	METABO
<b>Manufacturer Part Number</b>	600663500
<b>Model</b>	KHE 2660 Quick
<b>Manufacturer Article Number</b>	600663500
<b>Battery included</b>	No
<b>Max. impact energy</b>	3 J
<b>Max. impact rate</b>	4300 rpm
<b>Power input</b>	850 W
<b>Max. recommended drilling diameter in concrete</b>	26 mm
<b>Max. drilling diameter in wood</b>	32 mm
<b>Max. drilling diameter in steel</b>	13 mm
<b>Max. core drill bit diameter</b>	68 mm
<b>Idle speed 1st gear min./max.</b>	0-1100 rpm
<b>Weight</b>	3.1 kg
<b>With rubber-coated handle</b>	Yes
<b>With electronic feedback</b>	No
<b>With soft start</b>	No
<b>With restart protection</b>	No
<b>Gross Weight</b>	6.050 kg
<b>Product Group</b>	745

### EAN

4007430306241