

Fusedrawer for Fuse Links 5x20 mm resp. 6.3x32 mm



Fuse drawer "Fingergrip" with voltage selector
 (Fuse links not enclosed)

Fuse drawer "Extrasafe" without voltage selector
 (Fuse links not enclosed)

Approvals and Compliances

Description

- Component :
 Snap-in , Rear Mounting
- 2 Functions :
 Fuseholder for Fuse-links 5x20 mm or 6.3x32 mm , Voltage selector insert
- Approved together with power entry module

Characteristics

- Fuse drawer meets requirements of medical standard IEC/EN 60601-1
- Suitable for use in equipment according to IEC/UL 60950

Other versions on request

- Fuse drawer with other voltage values

References

Fits to type: [CD](#); [CD-Bowdencable](#); [KD](#); [KD-Bowdencable](#); [KEC](#); [KFC](#)

Weblinks

[pdf datasheet](#), [html-datasheet](#), [General Product Information](#), [Distributor-Stock-Check](#), [Accessories](#), [Detailed request for product](#)

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [Details about Approvals](#)

Application standards

Application standards where the product can be used

| Organization | Design | Standard | Description |
|--------------|--------------------------------|--------------|---|
| | Designed for applications acc. | IEC/UL 60950 | IEC 60950-1 includes the basic requirements for the safety of information technologyequipment. |
| | Designed for applications acc. | IEC 60601-1 | Medical electrical equipment - Part 1: General requirements for basic safety and essential performance |
| | Designed for applications acc. | IEC 60335-1 | Safety of electrical appliances for household and similar purposes. Meets the requirements for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-12 and -13. |

Compliances

The product complies with following Guide Lines

| Identification | Details | Initiator | Description |
|----------------|-------------------|-------------|---|
| | RoHS | SCHURTER AG | EU Directive RoHS 2011/65/EU |
| | China RoHS | SCHURTER AG | The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS. |
| | REACH | SCHURTER AG | On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force. |
| | Medical Equipment | SCHURTER AG | Suitable for use in medical equipment according to IEC/UL 60601-1 |

Voltage Selector Inserts

| yy | KEC KD | Marking on Voltage Selector Insert / Terminal No. | | | |
|--------------|-----------|---|--------|--------|--------|
| | | 1 3 | 2 4 | 3 5 | 4 6 |
| 4303.2014.00 | | - | - | - | - |
| 4303.2014.01 | | 100 | 120 | 220 | 240 |
| 4303.2014.02 | | 110 | 150 | 220 | - |
| 4303.2014.03 | | 110 | - | 220 | - |
| 4303.2014.04 | | 110 | 220 | 240 | - |
| 4303.2014.05 | | 115 | - | 230 | - |
| 4303.2014.06 | | 117 | 220 | 240 | - |
| 4303.2014.08 | | 110 V | - | 220 V | - |
| 4303.2014.09 | | 220 | - | 240 | - |
| 4303.2014.11 | | 110 | 120 | 220 | 240 |
| 4303.2014.12 | | 115 | 230 | 240 | - |
| 4303.2014.13 | | 100 | 110 | 220 | 240 |
| 4303.2014.14 | | 100 | 117 | 220 | 240 |
| 4303.2014.15 | | 100 | 115 | 230 | - |
| 4303.2014.16 | | 100 | 120 | 230 | 240 |
| 4303.2014.17 | | 115 | 120 | 230 | 240 |
| 4303.2014.19 | | 220 | 120 | 240 | 230 |
| 4303.2014.20 | | 100 | 120 | 230 | - |
| 4303.2014.21 | | 100 | - | 220 | - |
| 4303.2014.22 | | 100 | 120 | 220 | 230 |
| 4303.2014.24 | | 200 | 220 | 240 | - |
| 4303.2014.27 | | 115 | 200 | 230 | - |
| 4303.2014.32 | | 100 | 110 | 230 | 240 |
| 4303.2014.34 | | 110 | 115 | 230 | 240 |
| 4303.2014.35 | | 100 | 115 | 230 | 240 |
| 4303.2014.36 | | 100 | 110 | 200 | 230 |
| 4303.2014.42 | | 100 | 115 | 120 | 230 |
| 4303.2014.46 | | 100 | 120 | 200 | 230 |
| 4303.2024.00 | | - | - | - | - |
| 4303.2024.01 | | 100 | 120 | 220 | 240 |
| 4303.2024.02 | | 110 | 150 | 220 | - |
| 4303.2024.03 | | 110 | - | 220 | - |
| 4303.2024.04 | | 110 | 220 | 240 | - |
| 4303.2024.05 | | 115 | - | 230 | - |
| 4303.2024.06 | | 117 | 220 | 240 | - |
| 4303.2024.08 | | 110 V | - | 220 V | - |
| 4303.2024.09 | | 220 | - | 240 | - |
| 4303.2024.10 | | 115 | 220 | 240 | - |
| 4303.2024.11 | | 110 | 120 | 220 | 240 |
| 4303.2024.12 | | 115 | 230 | 240 | - |
| 4303.2024.15 | | 100 | 115 | 230 | - |
| 4303.2024.16 | | 100 | 120 | 230 | 240 |
| 4303.2024.17 | | 115 | 120 | 230 | 240 |
| 4303.2024.18 | | 115 | - | 240 | - |
| 4303.2024.19 | | 220 | 120 | 240 | 230 |
| 4303.2024.20 | | 100 | 120 | 230 | - |
| 4303.2024.22 | | 100 | 120 | 220 | 230 |
| 4303.2024.25 | | 120 | - | 230 | - |
| 4303.2024.28 | | - | 230 | 240 | - |
| 4303.2024.30 | | 117 | 220 | 240 | 100 |
| 4303.2024.31 | | 117 | 220 | 240 | 100 |
| 4303.2024.35 | | 100 | 115 | 230 | 240 |
| 4303.2024.40 | | 100 | 110 | 127 | 230 |
| 4303.2024.44 | | 100 | 115 | 127 | 230 |

| yy | KEC KD | Marking on Voltage Selector Insert / Terminal No. | | | |
|----------------|-----------|---|--------|--------|--------|
| | | 1 3 | 2 4 | 3 5 | 4 6 |
| 4303.2024.45 | | 100 | 115 | 230 | 127 |
| 4303.2024.46 | | 100 | 120 | 200 | 230 |
| 4303.2036.01 | | 100 | 120 | 220 | 240 |
| 4303.2036.01.1 | | 100 | 120 | 220 | 240 |
| 4303.2036.03 | | 110 | - | 220 | - |
| 4303.2036.04 | | 110 | 220 | 240 | - |
| 4303.2036.05 | | 115 | - | 230 | - |
| 4303.2036.11 | | 110 | 120 | 220 | 240 |
| 4303.2036.23 | | 100 | 110 | 120 | - |
| 4303.2037.01 | | 100 | 120 | 220 | 240 |
| 4303.2037.03 | | 110 | - | 220 | - |
| 4303.2037.10 | | 115 | 220 | 240 | - |
| 4303.2037.13 | | 100 | 110 | 220 | 240 |
| 4303.2114.01 | | 100 | 120 | 220 | 240 |
| 4303.2114.02 | | 110 | 150 | 220 | - |
| 4303.2114.03 | | 110 | - | 220 | - |
| 4303.2114.04 | | 110 | 220 | 240 | - |
| 4303.2114.05 | | 115 | - | 230 | - |
| 4303.2114.08 | | 110 V | - | 220 V | - |
| 4303.2114.09 | | 220 | - | 240 | - |
| 4303.2114.11 | | 110 | 120 | 220 | 240 |
| 4303.2114.12 | | 115 | 230 | 240 | - |
| 4303.2114.13 | | 100 | 110 | 220 | 240 |
| 4303.2114.15 | | 100 | 115 | 230 | - |
| 4303.2114.17 | | 115 | 120 | 230 | 240 |
| 4303.2114.20 | | 100 | 120 | 230 | - |
| 4303.2114.22 | | 100 | 120 | 220 | 230 |
| 4303.2114.29 | | 100 | 117 | 125 | - |
| 4303.2114.43 | | 115 | - | 230 | - |
| 4303.2114.48 | | 100 | 120 | 208 | 230 |
| 4303.2124.00 | | - | - | - | - |
| 4303.2124.01 | | 100 | 120 | 220 | 240 |
| 4303.2124.02 | | 110 | 150 | 220 | - |
| 4303.2124.03 | | 110 | - | 220 | - |
| 4303.2124.04 | | 110 | 220 | 240 | - |
| 4303.2124.05 | | 115 | - | 230 | - |
| 4303.2124.12 | | 115 | 230 | 240 | - |
| 4303.2124.15 | | 100 | 115 | 230 | - |
| 4303.2124.16 | | 100 | 120 | 230 | 240 |
| 4303.2124.19 | | 220 | 120 | 240 | 230 |
| 4303.2124.22 | | 100 | 120 | 220 | 230 |
| 4303.2124.23 | | 100 | 110 | 120 | - |
| 4303.2124.37 | | 115 | 230 | 240 | 100 |
| 4303.2124.39 | | 220 | 230 | 240 | - |
| 4303.2401 | | - | - | - | - |
| 4303.2403 | | - | - | - | - |
| 4303.2406 | | - | - | - | - |
| 4303.2408 | | - | - | - | - |
| 4303.2411 | | - | - | - | - |
| 4303.2413 | | - | - | - | - |
| 4303.2416 | | - | - | - | - |
| 4303.2514.01 | | 100 | 120 | 220 | 240 |
| 4303.2514.02 | | 110 | 150 | 220 | - |
| 4303.2514.03 | | 110 | - | 220 | - |

| yy | KEC KD | Marking on Voltage Selector Insert / Terminal No. | | | |
|--------------|-----------|---|--------|--------|--------|
| | | 1 3 | 2 4 | 3 5 | 4 6 |
| 4303.2514.05 | | 115 | - | 230 | - |
| 4303.2514.08 | | 110 V | - | 220 V | - |
| 4303.2514.15 | | 100 | 115 | 230 | - |
| 4303.2514.16 | | 100 | 120 | 230 | 240 |
| 4303.2514.17 | | 115 | 120 | 230 | 240 |
| 4303.2514.18 | | 115 | - | 240 | - |
| 4303.2514.23 | | 100 | 110 | 120 | - |
| 4303.2514.38 | | 110 | 230 | 220 | 240 |
| 4303.2524.01 | | 100 | 120 | 220 | 240 |
| 4303.2524.04 | | 110 | 220 | 240 | - |
| 4303.2524.05 | | 115 | - | 230 | - |
| 4303.2524.16 | | 100 | 120 | 230 | 240 |
| 4303.2524.20 | | 100 | 120 | 230 | - |
| 4303.2524.23 | | 100 | 110 | 120 | - |
| 4303.2524.25 | | 120 | - | 230 | - |
| 4303.2536.46 | | 100 | 120 | 200 | 230 |
| 4303.2537.46 | | 100 | 120 | 200 | 230 |
| 4303.2614.01 | | 100 | 120 | 220 | 240 |
| 4303.2614.02 | | 110 | 150 | 220 | - |
| 4303.2614.03 | | 110 | - | 220 | - |
| 4303.2614.04 | | 110 | 220 | 240 | - |
| 4303.2614.09 | | 220 | - | 240 | - |
| 4303.2614.15 | | 100 | 115 | 230 | - |
| 4303.2614.23 | | 100 | 110 | 120 | - |
| 4303.2614.28 | | - | 230 | 240 | - |
| 4303.2624.01 | | 100 | 120 | 220 | 240 |
| 4303.2624.03 | | 110 | - | 220 | - |
| 4303.2624.04 | | 110 | 220 | 240 | - |
| 4303.2624.22 | | 100 | 120 | 220 | 230 |
| 4303.2714.08 | | 110 V | - | 220 V | - |
| 4303.2737.01 | | 100 | 120 | 220 | 240 |
| 4303.2737.05 | | 115 | - | 230 | - |
| 4303.2737.06 | | 117 | 220 | 240 | - |
| 4303.2901 | | - | - | - | - |
| 4303.2903 | | - | - | - | - |
| 4303.2906 | | - | - | - | - |
| 4303.2908 | | - | - | - | - |
| 4303.2911 | | - | - | - | - |
| 4303.2913 | | - | - | - | - |

Index "yy" matches the last two characters of the Order Number within the Variants

All Variants

| Mounting | Fuse-Link | Fuseholder | Comment | Order Number |
|------------|-----------|------------|---------|--------------|
| Fingergrip | 5 x 20 | 1-pole | - | 4303.2114.01 |
| Fingergrip | 5 x 20 | 1-pole | - | 4303.2114.02 |
| Fingergrip | 5 x 20 | 1-pole | - | 4303.2114.03 |
| Fingergrip | 5 x 20 | 1-pole | - | 4303.2114.04 |
| Fingergrip | 5 x 20 | 1-pole | - | 4303.2114.05 |
| Fingergrip | 5 x 20 | 1-pole | - | 4303.2114.08 |
| Fingergrip | 5 x 20 | 1-pole | - | 4303.2114.09 |
| Fingergrip | 5 x 20 | 1-pole | - | 4303.2114.11 |
| Fingergrip | 5 x 20 | 1-pole | - | 4303.2114.12 |

| Mounting | Fuse-Link | Fuseholder | Comment | Order Number |
|------------|-----------|------------|-----------------|--------------|
| Fingergrip | 5 x 20 | 1-pole | - | 4303.2114.15 |
| Fingergrip | 5 x 20 | 1-pole | - | 4303.2114.17 |
| Fingergrip | 5 x 20 | 1-pole | - | 4303.2114.20 |
| Fingergrip | 5 x 20 | 1-pole | - | 4303.2114.22 |
| Fingergrip | 5 x 20 | 1-pole | - | 4303.2114.29 |
| Fingergrip | 5 x 20 | 1-pole | - | 4303.2114.43 |
| Fingergrip | 5 x 20 | 1-pole | - | 4303.2114.48 |
| Extra-Safe | 5 x 20 | 1-pole | - | 4303.2124.00 |
| Extra-Safe | 5 x 20 | 1-pole | - | 4303.2124.01 |
| Extra-Safe | 5 x 20 | 1-pole | - | 4303.2124.03 |
| Extra-Safe | 5 x 20 | 1-pole | - | 4303.2124.04 |
| Extra-Safe | 5 x 20 | 1-pole | - | 4303.2124.05 |
| Extra-Safe | 5 x 20 | 1-pole | - | 4303.2124.12 |
| Extra-Safe | 5 x 20 | 1-pole | - | 4303.2124.15 |
| Extra-Safe | 5 x 20 | 1-pole | - | 4303.2124.19 |
| Extra-Safe | 5 x 20 | 1-pole | - | 4303.2124.22 |
| Extra-Safe | 5 x 20 | 1-pole | - | 4303.2124.23 |
| Extra-Safe | 5 x 20 | 1-pole | - | 4303.2124.37 |
| Extra-Safe | 5 x 20 | 1-pole | - | 4303.2124.39 |
| Fingergrip | 5 x 20 | 1-pole | - | 4303.2406 |
| Extra-Safe | 5 x 20 | 1-pole | - | 4303.2408 |
| Fingergrip | 5 x 20 | 1-pole | spare fuse case | 4303.2416 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.00 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.01 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.02 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.03 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.04 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.05 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.06 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.08 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.09 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.11 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.12 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.13 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.15 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.16 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.17 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.19 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.20 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.21 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.22 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.24 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.27 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.34 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.35 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.36 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2014.42 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.00 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.01 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.02 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.03 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.04 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.05 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.06 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.08 |

| Mounting | Fuse-Link | Fuseholder | Comment | Order Number |
|------------|-----------|------------|----------------------------------|----------------|
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.09 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.10 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.11 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.12 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.15 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.16 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.17 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.18 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.19 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.20 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.22 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.25 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.28 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.30 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.35 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.40 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.44 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.45 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2024.46 |
| Fingergrip | 5 x 20 | 2-pole | - | 4303.2401 |
| Extra-Safe | 5 x 20 | 2-pole | - | 4303.2403 |
| Fingergrip | 5 x 20 | 2-pole | shorting bar on the neutral side | 4303.2036.01 |
| Fingergrip | 5 x 20 | 2-pole | shorting bar on the neutral side | 4303.2036.01.1 |
| Fingergrip | 5 x 20 | 2-pole | shorting bar on the neutral side | 4303.2036.03 |
| Fingergrip | 5 x 20 | 2-pole | shorting bar on the neutral side | 4303.2036.04 |
| Fingergrip | 5 x 20 | 2-pole | shorting bar on the neutral side | 4303.2036.05 |
| Fingergrip | 5 x 20 | 2-pole | shorting bar on the neutral side | 4303.2036.11 |
| Fingergrip | 5 x 20 | 2-pole | shorting bar on the neutral side | 4303.2036.23 |
| Extra-Safe | 5 x 20 | 2-pole | shorting bar on the neutral side | 4303.2037.01 |
| Extra-Safe | 5 x 20 | 2-pole | shorting bar on the neutral side | 4303.2037.03 |
| Extra-Safe | 5 x 20 | 2-pole | shorting bar on the neutral side | 4303.2037.10 |
| Extra-Safe | 5 x 20 | 2-pole | shorting bar on the neutral side | 4303.2037.13 |
| Fingergrip | 5 x 20 | 2-pole | shorting bar on the neutral side | 4303.2411 |
| Extra-Safe | 5 x 20 | 2-pole | shorting bar on the neutral side | 4303.2413 |
| Fingergrip | 6.3 x 32 | 1-pole | - | 4303.2614.01 |
| Fingergrip | 6.3 x 32 | 1-pole | - | 4303.2614.02 |
| Fingergrip | 6.3 x 32 | 1-pole | - | 4303.2614.03 |
| Fingergrip | 6.3 x 32 | 1-pole | - | 4303.2614.04 |
| Fingergrip | 6.3 x 32 | 1-pole | - | 4303.2614.09 |
| Fingergrip | 6.3 x 32 | 1-pole | - | 4303.2614.23 |
| Fingergrip | 6.3 x 32 | 1-pole | - | 4303.2614.28 |
| Extra-Safe | 6.3 x 32 | 1-pole | - | 4303.2624.01 |
| Extra-Safe | 6.3 x 32 | 1-pole | - | 4303.2624.03 |
| Extra-Safe | 6.3 x 32 | 1-pole | - | 4303.2624.04 |
| Extra-Safe | 6.3 x 32 | 1-pole | - | 4303.2624.22 |
| Fingergrip | 6.3 x 32 | 1-pole | - | 4303.2906 |
| Extra-Safe | 6.3 x 32 | 1-pole | - | 4303.2908 |
| Fingergrip | 6.3 x 32 | 2-pole | - | 4303.2514.01 |
| Fingergrip | 6.3 x 32 | 2-pole | - | 4303.2514.02 |
| Fingergrip | 6.3 x 32 | 2-pole | - | 4303.2514.03 |
| Fingergrip | 6.3 x 32 | 2-pole | - | 4303.2514.05 |
| Fingergrip | 6.3 x 32 | 2-pole | - | 4303.2514.08 |
| Fingergrip | 6.3 x 32 | 2-pole | - | 4303.2514.15 |
| Fingergrip | 6.3 x 32 | 2-pole | - | 4303.2514.16 |
| Fingergrip | 6.3 x 32 | 2-pole | - | 4303.2514.17 |

| Mounting | Fuse-Link | Fuseholder | Comment | Order Number |
|------------|-----------|------------|----------------------------------|--------------|
| Fingergrip | 6.3 x 32 | 2-pole | - | 4303.2514.18 |
| Fingergrip | 6.3 x 32 | 2-pole | - | 4303.2514.23 |
| Fingergrip | 6.3 x 32 | 2-pole | - | 4303.2514.38 |
| Extra-Safe | 6.3 x 32 | 2-pole | - | 4303.2524.01 |
| Extra-Safe | 6.3 x 32 | 2-pole | - | 4303.2524.04 |
| Extra-Safe | 6.3 x 32 | 2-pole | - | 4303.2524.05 |
| Extra-Safe | 6.3 x 32 | 2-pole | - | 4303.2524.16 |
| Extra-Safe | 6.3 x 32 | 2-pole | - | 4303.2524.20 |
| Extra-Safe | 6.3 x 32 | 2-pole | - | 4303.2524.23 |
| Fingergrip | 6.3 x 32 | 2-pole | - | 4303.2901 |
| Extra-Safe | 6.3 x 32 | 2-pole | - | 4303.2903 |
| Fingergrip | 6.3 x 32 | 2-pole | shorting bar on the neutral side | 4303.2536.46 |
| Extra-Safe | 6.3 x 32 | 2-pole | shorting bar on the neutral side | 4303.2537.46 |
| Fingergrip | 6.3 x 32 | 2-pole | shorting bar on the neutral side | 4303.2911 |
| Extra-Safe | 6.3 x 32 | 2-pole | shorting bar on the neutral side | 4303.2913 |

Most Popular.

Availability for all products can be searched real-time: <https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

"yy" see Voltage Selector Inserts Table

Packaging unit 50 Pcs