



**MATERIAL LIST:**

⑧	Bottom Panel:	Fireproof PC/ABS(metalized)	1	
⑦	Upper Panel Cover:	Fireproof PC/ABS(metalized)	1	
⑥	RJ-45 JackShield:	0.25mm thickness Brass with Ni plated	2	
⑤	RJ-45 Jack:	Housing-PBT/FTP 8P8C 3u" gold plated	2	
④	PCB:	FR-4/1.6mm UL-94V0	1	
③	Cable:	CAT.5E SFTP Cable(Gray)	1	
②	Cable boot:	PVC (Gray)	2	
①	Connector:	RJ45 8P8C PLUG GOLD PLATED 3u"	1	
NO.			QT'Y	REMARK

**NOTES:**

Electrical Specifications:

Insulation Resistance: 500M ohms (min.)

Contact Resistance: 20M ohms (max.)

Current Rating : 1.5 Amps.

DC Resistance: 0.1 ohms(max.)

Withstanding Voltage : 1000 VAC RMS @ 60Hz/ 1 min.

Mechanical Specifications:

RJ-45 Jack Insertion Cycle : Over 750 Cycles (min.)

RoHS 2.0 And REACH Compliant

OPERATING TEMPERATURE:-10°C ~ 60°C

STORAGE TEMPERATURE:-20°C ~ 75°C

		CUSTOMER		CN		ITEM NO.		2269070	
		PRODUCT NAME		ISDN T-Adapter cable 1×RJ45 Plug to 2×RJ45 Socket 1:1		[REDACTED]		275003 UNIT MM	
		NEW		2018-03-14		A		DRAWNBY CHECKBY APPOBY DATE	
BY		CHK		DATE		REV.		Alvan Alvan 2018-03-14	
REVISION RECORD MODIFICATIONS									