


No.	Changes and/or Note No.	Date	Sign	No.	Changes and/or Note No.	Date	Sign



UNIT: (mm)

### DIMENSIONS

Size:	A	B	C	D	Part No:
09P	30.80	24.99	16.30	19.20	2101-0180-11
15P	39.15	33.32	24.65	27.70	2101-0180-12
25P	53.00	47.04	38.40	41.10	2101-0180-13
37P	69.30	63.50	54.80	57.30	2101-0180-14
50P					On Request

### MATERIAL SPECIFICATIONS:

Shell: Steel, Tin or Ni Plated (With Dimples)  
Zinc Plated (Without Dimples)  
Insulator: Glass Filled PBT, UL 94 V-0  
Contacts: Brass, Stamped Pins  
Gold over Nickel  
Rivet: Copper-Alloy, Ni Plated


### TECHNICAL SPECIFICATIONS:

Current Rating:  
Contact Resistance: 15 mΩ Max.  
Insulator Resistance: 1000 MΩ Min.  
Test Voltage: 500V AC for 1 Minute  
Operating Temperature: -55°C to +105°C

DATE 2011-06-10	DRAWN MRR	SCALE	MATERIAL TYPE
	APPROVED		REPLACES



DBxx-SS  
Sub-D Female, Solder Cup



DRAWING No.

2101-0180-1x