



NOTE:

1. Material: contacts: C2680 EH T=0.20
insulator: PBT
shell: SPCC T=0.35

2.Specification:

- 2.1 Current rating: 1 A Max.
- 2.2 Dielectric withstanding voltage: 500 V(ac) for 1 minute.
- 2.3 Contact resistance: 30 mΩ Max.
- 2.4 Insulation resistance: 1000 MΩ Min at DC 500V.
- 2.5 Temperature range: -55°C~+85°C.
- 2.6 Insertion Force: 3.57 kgf max.
- 2.7 Extraction Force: 1.02 kgf min.
- 2.8 Durability:1500 cycles at 200±50 cycles per hour.

3.Finishes:

- 3.1 Contacts: a:半金錫,銀底50"min, 鍍錫100"min,
接觸點鍍金 1u".3u".5u".15u".30u".
- 3.2 Shell: 鍍鎳:銅底50u"min,鎳80u"min.

RoHS Compliant		HSM 玄茂科技股份有限公司 HSUAN MAO TECHNOLOGY CO., LTD.	
APPD. 核准		TOLERANCE 容許公差 0 ± 0.25 .00 ± ANG ±	PART NAME 品名 USB A TPYE 4P MALE SOLDER TYPE ROHS
DWG. 製圖 <i>Helen</i>	SCALE 比例 參考	UNIT 單位 MM	PART NO. 料號 C8319-04AMSXX0R
DATE 制表日 2015/3/20	PAGE 張數 1 OF 1	REV. 版本 A	