















h
Q

Easy life solutions

**Lighting
assortment
2016-17**



HALOGEN

Shape	Part number	Article Header	Base	Wattage	Wattage equivalent	Rated luminous flux	Dimmable	Colour temperature	Rated life time of lamp	Voltage	Energy class
	HQHE14BALL001	HQ halogen lamp ball E14 18 W 205 lm 2800K	E14	18 W	25 W	205 lm	Yes	2800 K	1500 h	230 V	D
	HQHE14BALL002	HQ halogen lamp ball E14 28 W 370 lm 2800K	E14	28 W	40 W	370 lm	Yes	2800 K	2000 h	230 V	D
	HQHE14BALL003	HQ halogen lamp ball E14 42 W 630 lm 2800K	E14	42 W	60 W	630 lm	Yes	2800 K	2000 h	230 V	D
	HQHE14CAND001	HQ halogen lamp candle E14 28 W 370 lm 2800 K	E14	28 W	40 W	370 lm	Yes	2800 K	2000 h	230 V	D
	HQHE14R50001	HQ halogen lamp R50 E14 42 W 375lm 2800K	E14	42 W	60 W	375 lm	Yes	2800 K	1500 h	230 V	D
	HQHE14R50002	HQ halogen lamp R50 E14 28 W 250 lm 2800K	E14	28 W	40 W	250 lm	Yes	2800 K	2000 h	230 V	D
	HQHE27BALL001	HQ halogen lamp ball E27 18 W 205 lm 2800K	E27	18 W	25 W	205 lm	Yes	2800 K	1500 h	230 V	D
	HQHE27BALL002	HQ halogen lamp ball E27 28 W 370 lm 2800K	E27	28 W	40 W	370 lm	Yes	2800 K	2000 h	230 V	D
	HQHE27BALL003	HQ halogen lamp ball E27 42 W 630 lm 2800 K	E27	42 W	60 W	630 lm	Yes	2800 K	2000 h	230 V	D
	HQHE27CLAS001	HQ halogen lamp classic GLS E27 18 W 205 lm 2800K	E27	18 W	25 W	205 lm	Yes	2800 K	1500 h	230 V	D
	HQHE27CLAS002	HQ halogen lamp classic GLS E27 28 W 370 lm 2800 K	E27	28 W	40 W	370 lm	Yes	2800 K	2000 h	230 V	D
	HQHE27CLAS003	HQ halogen lamp classic GLS E27 42 W 630 lm 2800K	E27	42 W	60 W	630 lm	Yes	2800 K	2000 h	230 V	D
	HQHE27CLAS004	HQ halogen lamp classic GLS E27 53W 850 lm 2800K	E27	53 W	75 W	850 lm	Yes	2800 K	2000 h	230 V	D
	HQHE27CLAS005	HQ halogen lamp ball E27 70 W 1 200 lm 2800 K	E27	70 W	100 W	1200 lm	Yes	2800 K	2000 h	230 V	D
	HQHE27R63002	HQ halogen lamp R63 E27 28 W 330 lm 2800K	E27	28 W	40 W	330 lm	Yes	2800 K	2000 h	230 V	D
	HQHE27R63003	HQ halogen lamp R63 E27 42 W 500 lm 2800K	E27	42 W	60 W	500 lm	Yes	2800 K	2000 h	230 V	D
	HQHE27R63004	HQ halogen lamp R63 E27 53W 620 lm 2800K	E27	53 W	70 W	620 lm	Yes	2800 K	2000 h	230 V	D
	HQHECO30001	HQ halogen lamp ECO30 28 W 370 lm 2800K		28 W	40 W	370 lm	Yes	2800 K	2000 h	230 V	
	HQHG4CAPS001	HQ halogen lamp capsule G4 5 W 35 lm 2800K	G4	5 W		35 lm	Yes	2800 K	2000 h	12 V	C
	HQHG4CAPS002	HQ halogen lamp capsule G4 10 W 105 lm 2800 K	G4	10 W		105 lm	Yes	2800 K	2000 h	12 V	C
	HQHG4CAPS003	HQ halogen lamp capsule G4 16 W 230 lm 2800K	G4	16 W	25 W	230 lm	Yes	2800 K	2000 h	12 V	C
	HQHG4CAPS004	HQ halogen lamp capsule G4 20 W 260 lm 2800K	G4	20 W		260 lm	Yes	2800 K	2000 h	12 V	C
	HQHG635CAPS001	HQ halogen lamp capsule G6.35 20 W 250 lm 2800K	GY6.35	20 W		250 lm	Yes	2800 K	2000 h	12 V	C
	HQHG635CAPS002	HQ halogen lamp capsule G6.35 35 W 430 lm 2800K	GY6.35	35 W		430 lm	Yes	2800 K	2000 h	12 V	C
	HQHG9CAPS001	HQ halogen lamp capsule G9 18 W 205 lm 2800K	G9	18 W		205 lm	Yes	2800 K	1500 h	230 V	D
	HQHG9CAPS002	HQ halogen lamp capsule G9 28 W 370 lm 2800 K	G9	28 W		370 lm	Yes	2800 K	2000 h	230 V	D
	HQHG9CAPS003	HQ halogen lamp capsule G9 42 W 630 lm 2800K	G9	42 W		630 lm	Yes	2800 K	2000 h	230 V	D
	HQHGU10MR16002	HQ halogen lamp MR16 GU10 42 W 223lm 2800K	GU10	42 W	60 W	223 lm	Yes	2800 K	2000 h	230 V	D
	HQHGU10MR16003	HQ halogen lamp MR16 GU10 20 W 77lm 2800K	GU10	20 W		77 lm	Yes	2800 K	2000 h	230 V	D
	HQHGU10MR16004	HQ halogen lamp MR16 GU10 35 W 173 lm 2800 K	GU10	35 W		173 lm	Yes	2800 K	2000 h	230 V	D
	HQHGU10MR16005	HQ halogen lamp MR16 GU10 50 W 282 lm 2800 K	GU10	50 W		282 lm	Yes	2800 K	2000 h	230 V	D
	HQHGU4MR11001	HQ halogen lamp MR11 GU4 20 W 201 lm 2800K		20 W		201 lm	Yes	2800 K	2000 h	12 V	B
	HQHGU4MR11002	HQ halogen lamp MR11 GU4 35 W 427 lm 2800K		35 W		427 lm	Yes	2800 K	2000 h	12 V	B
	HQHGU53MR16001	HQ halogen lamp MR16 GU5.3 35 W 427 lm 2800K	GU5.3	35 W		427 lm	Yes	2800 K	2000 h	12 V	B
	HQHGU53MR16002	HQ halogen lamp MR16 GU5.3 50 W 673 lm 2800K	GU5.3	50 W		673 lm	Yes	2800 K	2000 h	12 V	B
	HQHR7SJ118001	HQ halogen lamp J118 R7S 160 W 3000 lm 2800K	R7s	160 W		3000 lm	Yes	2800 K	2000 h	230 V	C
	HQHR7SJ118002	HQ halogen lamp J118 R7S 230 W 4650 lm 2800K	R7s	230 W		4650 lm	Yes	2800 K	2000 h	230 V	C
	HQHR7SJ118003	HQ halogen lamp J118 R7S 400 W 8545 lm 2800K	R7s	400 W		8545 lm	Yes	2800 K	2000 h	230 V	C
	HQHR7SJ78001	HQ halogen lamp J78 R7S 120 W 2220 lm 2800K	R7s	120 W		2220 lm	Yes	2800 K	2000 h	230 V	C