

# IDC Ribbon Cable Socket

## 8P



### FEATURES:

IDC transition connectors for use with ribbon cable with a 1.27 mm pitch

### SPECIFICATION:

Poles	8
Pitch	2.54 mm
Gender of contacts	Female
Rated current	1 A
Rated voltage	250 V
Housing Material	Glass fibre (GF)/Polybutylene terephthalate (PBT)
Contact material	Gold-plated
Test voltage	0.5 kV
Temperature range	-40...+85 °C
Combustibility class	UL 94 V-0



### Art. Nr.

RND 205-00681

