




"RAC" HEATERS WITH CABLE

Description: 45/60/80/100/150 W



Heating element: PTC thermistor, self regulating
Heat sink: black anodised extruded aluminium profile
Method of mounting: snap-on fixing on RAIL 35mm DIN 46 277/3 EN 50 022
Rated temperature range: from -30°C to +40°C
Storage temp. range: from -40°C to +90°C
Protection degree by heaters: IP50
Electrical connection: by 3 poles cable L-N-PE
External cable: 3x20AWG cable with silicone rubber sheath 500 mm length
Appliance class: class I
Over voltage categories: III as IEC 60664-1 standard
Rated voltage: 230 V a.c./d.c.
Rated voltage range: 110-250 V a.c./d.c.
Rated frequency: 50/60 Hz
Max voltage: 265 V a.c./d.c.
Applicable standards: EN 60335-1
Approvals: CE

technical drawing



Model	Dimension		Heating Power*	Absorbed Current*	External Surface**	Internal Heat Sink**	Weight
	A [mm]	B [mm]					
RAC-100	152	58	100	475	105	130	0.44
RAC-45	102	34	45	200	70	90	0.31
RAC-60	102	34	60	260	85	105	0.31
RAC-80	152	58	80	390	90	110	0.44
RACS-150	152	58	150	770	125	145	0.44

*The values of heating power, absorbed current, were obtained at 230 Va.c. 50Hz and at ambient temperature condition of 15±5°C after a working of 10 minutes. These values have an uncertainty of 10%. ** Temperatures have been obtained after a working of 10 minutes at ambient temperature condition of 23.5°C.

All specifications, data and drawing are subject to change without notice and are approximate. Please refer to our terms of sales including our warranty and limited liabilities clause