

MODLINK MSDD DATA INSERT

1×SUB-D9 fem./fem.+ 1×RJ45+ 1×USB-A fem./male 0,7m

SUB-D9; RJ45; USB (form A)

1 × SUB-D9 (female/female); 1 × RJ45, 8-pole metal, CAT5e (female/female); 1 × USB (female/female/0.7 m cable) form A

[Link to Product](#)

Illustration



Product may differ from Image

General data

Dimensions H × W × D 88×51×45 mm

Insert 2

Article number	4000-68000-1420000
Operating voltage	SUB-D: max. 125 V AC/150 V DC; RJ4: max. 48 V AC/DC; RJ12: max. 48 V AC/DC; USB: max. 30 V AC/DC; PS2: max. 30 V AC/DC; DVI: max. 40 V AC
Operating current	SUB-D: max. 3 A; RJ45: max. 1 A; RJ12: max. 1 A; USB: max. 1 A; PS2: max. 1 A; DVI: max. 1.5 A
Connection cross section	SUB-D: max. 0.5 mm ² (AWG 20); PS2: max. 0.22 mm ² (AWG 24)
Locking of ports	SUB-D: UNC 4...40 bolt; RJ45: staple; RJ12: staple; USB: snap-in; PS2: snap-in
Specification	SUB-D: (DIN 41652/IEC 60807-1); RJ45: CAT5e (100 MHz - Mbit/s); USB: 2.0/Type 2dB (max. 480 Mbit/s)
Mounting depth mounted	SUB-D: approx. 32 mm; RJ45: approx. 32 mm; RJ12: approx. 32 mm; USB: approx. 80 mm; PS2: approx. 32 mm
Dimensions H × W × D	88×51×45
Shielded	yes

Commercial data

country of origin	CZ
customs tariff number	85369010
minimum order quantity	1