

Product type designation

Product description

Antenna cable for UHF, RP-TNC / RP-TNC

Coaxial cable

SIMATIC RF600 CONNECT. CABLE ANTENNA L3

PREASSEMBLED, BETWEEN READER AND ANTENNA, IP65 EU

AND USA-VERSION PE, CMR/MPR, LENGTH: 3 M



Suitability for use	Plug-in cable for connecting a UHF antenna to an RF600 reader
Cable designation	LMR-195
Cable length	3 m

Electrical data

Number of electrical connections	2
Type of electrical connection	RP-TNC (female, straight) / RP-TNC (female, straight)
Damping ratio per length <ul style="list-style-type: none"> • at 900 MHz / maximum 	0.365 dB/m
Impedance <ul style="list-style-type: none"> • Rated value 	50 Ω
Loop resistance per length / maximum	41 m Ω /m
Operating voltage <ul style="list-style-type: none"> • maximum 	1000 V

Mechanical data

Design of the shield	Braided shield made of tin-plated copper wires
Outer diameter <ul style="list-style-type: none"> • of cable sheath 	4.95 mm
Material <ul style="list-style-type: none"> • of inner conductor • of dielectric • of cable sheath 	Cu PE PE
Color <ul style="list-style-type: none"> • of cable sheath 	Black

Bending radius	
<ul style="list-style-type: none"> • with single bend / minimum permissible • with multiple bends / minimum permissible 	<p>12.7 mm</p> <p>50.8 mm</p>
Tensile load / maximum	180 N
Weight per length	30 kg/km

Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> • during operation • during storage • during transport • during installation 	<p>-40 ... +85 °C</p> <p>-70 ... +85 °C</p> <p>-40 ... +85 °C</p> <p>-40 ... +80 °C</p>
Burning behavior	flame resistant according to UL/NEC, CSA: CMR, FT4
Radiological resistance / to UV radiation	resistant

Product properties, functions, components / general

Product property	
<ul style="list-style-type: none"> • halogen-free 	Yes

Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAx Download Manager • to website: Industry Online Support 	<p>https://mall.industry.siemens.com</p> <p>http://www.siemens.com/automation/net/catalog</p> <p>http://automation.siemens.com/bilddb</p> <p>http://www.siemens.com/cax</p> <p>https://support.industry.siemens.com</p>

last modified: 16.03.2015