

PNOZ m B0

772100




Configurable control system PNOZmulti 2 base module expandable, 20 safe digital inputs, up to 8 of which can be configured as auxiliary outputs 4 safe semiconductor outputs.

Technical details

Approvals:	CE;cULus Listed;TÜV;BG
Base unit:	Yes
Number of digital inputs:	12
Number of configurable I/Os:	8
Number of test pulse outputs:	4
Supply voltage (V):	24,0
Supply voltage type:	DC
Terminal type:	Screw terminal;Spring-loaded terminal
Terminal style:	Plug-in
Version for extreme environ. conditions:	Standard
Supply voltage type:	0.8 W
Width dimension:	45.0 mm
Height dimension:	101.4 mm
Depth dimension:	120.0 mm
Gross weight:	250 g
Net weight:	235 g
Ambient temperature:	0 - 60 °C

Accessories



773010B

Basic License for PNOZmulti Config.



750008

PNOZ s Set1 screw terminals 45mm



751008

PNOZ s Set1 spring loaded terminals 45mm



779201

PNOZmulti Chipcard 1 piece 8kb



779211

Chipcard 1 piece 32kB

Optional accessories




312992

PSSu A USB-CAB03



312993

PSSu A USB-CAB05



773010K

User License for PNOZmulti Config



773010U

Basic Upgr License for PNOZmulti Config



773011B

Basic License for PNOZmulti Service




773011K

User License for PNOZmulti Service



773011U

Basic Upgr License for PNOZmulti Service



773011V

User Upgr License for PNOZmulti Service



779200

PNOZmulti Chipcard Set 10 piece 8KB



779212

PNOZmulti Chipcard Set 10 pieces 32kB



779230

PNOZ Chip Card Reader



779240

PNOZmulti Chipcard Holder (Sparepart)



779250

PNOZmulti Seal 12 pieces



779260

PNOZ mm0.xp connector left (10 pcs)



779261

PNOZ mm0.xp terminator left (10 pcs.)