



18W

VT-819 18W LED WALL LAMP COLORCODE:3000K WHITE BODY,IP44

Lumens 1800	Beam Angle 90	Dimensions 600x100x42mm
-----------------------	-------------------------	-----------------------------------

Warm White
SKU:8533

2 YEARS
WARRANTY

SENSOR
COMPATIBLE



Technical Information

Watts:	18	IP Rating:	IP44
Lumens:	1800	Dimmable:	No
On/Off Cycles:	>15000	Warranty (Years):	2
Beam Angle:	90	PF:	>0.5
Unit Color:	White	CRI:	>80
Body Type:	Aluminium	Operation Temperature:	-25 to +50°C
Long life:	20,000 Hours	Input Power:	AC:220-240V,50/60Hz
LED Chip Type:	SMD	Sensor Compatibility:	Yes

Features

- ✓ Modern Wall lights available in sleek and stylish designs.
- ✓ Excellent heat dissipation
- ✓ Available in different color options - Warm White and Day White
- ✓ Easy installation and Maintenance
- ✓ Application: Perfect for halls, pathways, Bedroom, Kitchen etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	1.608
Unit CBM	0.007168

Listing Details

EAN Code	3800157638678
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	10
Qty Per Pallet	160

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES