

SVUB boring bar, steel positive

for longitudinal and copy turning with VB indexable insert

ATORN[®]

Application


for longitudinal and copy turning with VB indexable insert, 35°

Version

- Precision-made boring bar, **steel**, with internal cooling, type V, attack angle 93°, tip angle 35°, clearance angle 5°

Advantage

- very slim geometry, optimised for contour turning work
- positive body geometry ensures low cutting forces



Art. No.	17855 118
ISO name	A40T SVUB R/L 16
Min. bore diameter	49 mm
Shaft diameter	40 mm
Clearance length	40 mm
Length	300 mm
Clamping surface height	38 mm
Suitable for indexable inserts	VB.. 1604..
Tool design	Right

EAN-Code

4050293562545