

Hydraulic jacks

Application:

For simple lifting of vehicles and components.

Execution:

- Steel, with pressure limiting valve to prevent overload.
- Models A, AX with one piston and one spindle.
- Models AT, ATDX with double piston
- ATN model with double telescopic piston for especially low overall height. Suitable for vehicles with limited ground clearance and confined space such as buses, low loaders, etc. The lever is operated horizontally, as vertical operation is often not possible with overhanging bodywork.
- Loading of the lever in axial direction only and over the entire surface extends the service life.
- Models AX 8-220, A 10-220, A 12-230, A 12-270, AX 15-230, AX 20-240, A 30-240, ATDX 3-185 and AT 5-215 with crown footprint.

Delivery:

1x hydraulic jack made of steel A 2-170 20 KN, 115 mm stroke.



Art. no.	29760 105
Model	AX20-240
Compressive force	200 kN
Construction height, retracted	240 mm
Lift height	155 mm
Spindle stroke	110 mm
Gross Weight	11.900 kg
Product Group	269