

Electronic micrometer

MICROMASTER IP54 with small measuring faces

 **TESA**

Application:

for measuring e.g. shaft diameters, external dimensions of workpieces etc.

Execution:

- carbide-tipped measuring faces
- Advanced friction coupling for consistent, repeatable measuring force
- Zero setting at any position
- mm/inch changeover
- AUTO OFF
- Preset function
- ABS function
- Display blocking function

Delivery:

In case, with battery (1 x 3 V lithium, type CR 2032), up to 100 mm



Art. no.	31469 010
Brand	TESA
Manufacturer Part Number	06030034
Display	Digital
Min./max. length measuring range	0-30 mm
Digit increment	0.001 mm
Measuring surface diameter	2 mm
IP protection class	IP 54
Data transmission type	RS232 opto coupled
Spindle clamping	Yes
Number of rechargeable batteries/batteries	1 PCS
Battery designation	3V CR2032 Lithium
DIN	863
Calibration Group	D
Gross Weight	0.775 kg
Product Group	362

EAN

7630041116380