

electronic pocket vernier calipers

Digital ABS point/fine callipers

Mitutoyo

Application:

For measuring, e.g. small grooves and grooves

Execution:

- Digimatic
- ABSOLUTE system for reliable measurement
- High-contrast display

Advantage:

- High resistance to water and dust (IP67 degree of protection)
- Extra finely ground measuring arms

Delivery:

Delivered in box



Art. no.	32018 082
Brand	MITUTOYO
Manufacturer Part Number	573-721-20
Min./max. length measuring range	0-150 mm
Min./max. length measuring range in inches	0-6 in
Data transmission type	DIGIMATIC
Depth gauge rod	Flat
IP protection class	IP 67
With drive wheel	Yes
Error limit	0.001 in
Length of jaw	40 mm
Design	Metric, Imperial
Digit height	9 mm
Length of cross tips	16.5 mm
Digit increment	0.01 mm
Digit increment in inches	0.0005 in
Type of locating	With locking screw
Preset function	No
With mm / inch switching	Yes
Length	233 mm
With automatic shut off	Yes
Battery designation	1,5 V SR44
Number of rechargeable batteries/batteries	1 PCS
Weight of rechargeable battery/battery	0.002 kg
Battery voltage	1.55 V
Type of rechargeable battery/battery	Silver oxide
Calibration Group	A
Functions	ABS function, Absolute function, Origin (Dimension preset), Auto-On/Auto-Off
Gross Weight	0.424 kg
Product Group	3MA

EAN

4946368726830