

## Dumper body, with floor-level emptying option

Carrying capacity 300 kg, without wheels

### Application:

For the collection and disposal of all types of bulk goods and solid materials with floor-level emptying option.

### Execution:

- Robust sheet steel structure with edge reinforcement
- Tiltable trough with handle
- Base frame with fork pockets
- Easily mobile using stacker
- Oil-resistant and watertight
- Protection against accidental slipping and tipping
- Optionally box-shaped or low trough
- All dimensions without wheels

### Advantage:

- With floor-level emptying option

### Delivery:

Goods supplied without packaging as standard. Packaging available for an additional charge.



<b>Art. no.</b>	<b>50266 275</b>
<b>Volume</b>	0.25 m <sup>3</sup>
<b>Length</b>	1320 mm
<b>Width</b>	670 mm
<b>Tipper edge height</b>	535 mm
<b>Height</b>	535 mm
<b>Fork pocket clearance</b>	285 mm
<b>Fork pocket size (W x H)</b>	170 x 55 mm
<b>With drain valve</b>	No
<b>With stacker seat tilt function</b>	No
<b>With perforated sheet</b>	No
<b>Load-carrying capacity</b>	300 kg
<b>Surface</b>	Zinc plated
<b>Gross Weight</b>	77.000 kg
<b>Product Group</b>	5AI

### EAN

4052462038882