

Cordless impact screwdriver ASCD 18-1000 W34 Select

With brushless motor and 6-stage torque adjustment. for metric fittings up to M27.



Application:

for metric fittings up to M27.

Execution:

- Robust solid metal shock transmission
- electronic torque setting in 6 steps prevents tearing of screw heads.
- FEIN SafetyCell Technology: Protects the battery and machine from overload, overheating and deep discharge

Advantage:

- Secure connection of the impact socket to the output square by means of force and form closure
- 130 screw joints (M27) with one battery charge (6 Ah)
- Maximum release torque of 1500 Nm in counter-clockwise rotation

Delivery:

Not including battery, not including charger in plastic case



Art. no.	71028 118
Brand	FEIN
Manufacturer Part Number	7 1150864000
Model	ASCD 18-1000 W34
Motor design	Brushless motor
Tool holding device	3/4-inch external square
Battery included	No
Battery voltage	18 V
Number of rechargeable batteries/batteries	0
Max. torque	1050 Nm
Torque levels	6
Max. impact rate	2200 rpm
Min. idle impact rate	0 rpm
Max. idle impact rate	2200 rpm
Min. idle speed	0 rpm
Max. idle speed	1800 rpm
Weight	3 kg
With battery capacity display	Yes
With rubber-coated handle	Yes
With overload protection	Yes
Sound-pressure level	93.6 dB
Vibration	12.9 m/s ²
Gross Weight	1.000 kg
Product Group	704

EAN

401458689 165 1