

NYS372P

Phono cable jack, nickel plated shell and contacts



Technical Information [▼hide](#)

Product

Title NYS372P

Electrical

Dielectric strength 0.5 kVdc

Insulation resistance $\geq 1 \text{ G}\Omega$

Rated current depends on mated connector

Contact resistance depends on mated connector

Mechanical

Cable O.D. 7.2 mm

Lifetime > 1000 mating cycles

Wiresize 26 AWG

Material

Insulation Thermoplastic

Environmental

Temperature range -25 °C to +70 °C