
KEMET Part Number: C320C102J1G5TA91707301



GoldMax 300 Auto COG, Ceramic, 1000 pF, 5%, 100 VDC, COG, GoldMax, Automotive Grade, Lead Spacing = 2.54mm



Dimensions	
L	5.08mm MAX
Н	5.84mm MAX
Т	3.18mm MAX
S	2.54mm +/-0.78mm
H0	16mm +/-0.5mm
F	0.51mm +0.1/-0.025mm

Packaging Specifications		
Packaging:	T&R, 305mm	
Packaging Quantity:	2500	

General Information	
Supplier:	KEMET
Series:	GoldMax 300 Auto C0G
Style:	Radial
Description:	GoldMax, Automotive Grade
Features:	Automotive Grade
RoHS:	Yes
Termination:	Tin
Failure Rate:	N/A
Qualifications:	AEC-Q200
AEC-Q200:	Yes
Halogen Free:	Yes

Specifications		
Capacitance:	1000 pF	
Capacitance Tolerance:	5%	
Voltage DC:	100 VDC	
Dielectric Withstanding Voltage:	250 VDC	
Temperature Range:	-55/+125C	
Temperature Coefficient:	COG	
Dissipation Factor:	0.10% 25C	
Aging Rate:	0% Loss/Decade Hour	
Insulation Resistance:	100 GOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

