


Type T PFA Insulated Flat Pair Thermocouple Cable



Features

- PFA Teflon® Insulated Flat Pair
- PFA Teflon® has a good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids, gasses, steam & pressure
- PTFE better for steam/elevated pressure environments



Specification

Cable Length	100 m
Cable Type	Laid Flat with PFA Jacket
Conductors	7
Conductor Cross Section	0.219 mm ²
Outer Colour	Brown
+ Colour	Brown
- Colour	White
Drain Wire	No
Insulation Material	PFA
Loop Resistance	2.3 Ohms
Max. Temperature	+260 °C
Min. Temperature	-75 °C
+ Conductor	Copper
- Conductor	Constantan
Screen	PET
Standards Met	Colour Code (Cores & Jacket) to IEC-584-3
Thermocouple Type	T
Tolerance	Class 1

Art. Nr.
RND 410-00069