

Schraubendreher

10768 ● Schraubendreher

mit Quergriff, für Innensechskantschrauben, Chrom-Vanadium, mattverchromt, schwarze Spitze.



Code	mm	L ₁ mm	L ₂ mm	g	Box
43 25 00 20	2	100	116	10	10
43 25 00 25	2,5	100	116	12	10
43 25 00 30	3	150	166	17	10
43 25 00 40	4	150	175	43	10
43 25 00 50	5	200	225	63	10
43 25 00 60	6	200	225	78	10
43 25 00 80	8	200	235	150	5
43 25 01 00	10	200	235	210	5

ES 10768/6



350 x 350 x 37 mm, 6-teilig

Code	g
96 83 81 19	780

Nr. 10768	SW 3; 4; 5; 6; 8; 10 mm
83 81 20 42	Einlage, leer 209

TCS 10768/8




350 x 350 x 40 mm, 8-teilig

Code	g
96 83 87 86	745

Nr. 10768	SW 2; 2,5; 3; 4; 5; 6; 8; 10 mm
-----------	---------------------------------

10768-2K ● Schraubendreher

mit 2-Komponenten-Quergriff, für Innensechskantschrauben, mit zwei Abtrieben, Chrom-Vanadium, mattverchromt, schwarze Spitze.



Code	mm	L ₁ mm	L ₂ mm	g	Box
43 25 20 20	2	100	125	33	10
43 25 20 25	2,5	100	125	42	10
43 25 20 30	3	150	174	42	10
43 25 20 40	4	150	176	51	10
43 25 20 50	5	200	227	73	10
43 25 20 60	6	200	228	92	10
43 25 20 80	8	200	235	178	5
43 25 21 00	10	200	235	247	5

TCS 10768-2K/6



350 x 350 x 40 mm, 6-teilig

Code	g
96 83 87 53	792

Nr. 10768-2K	SW 3; 4; 5; 6; 8; 10 mm
--------------	-------------------------

10769 ● TORX®-Schraubendreher

mit Quergriff, für Innen TORX®-Schrauben, Schaft über Nickel verchromt, Spitzen gehärtet, Chrom-Vanadium, mattverchromt, schwarze Spitze.



Code	Gr.	mm	L ₁ mm	L ₂ mm	g	Box
43 29 00 08	T8	2,3	80	96	12	5
43 29 00 09	T9	2,5	80	96	13	5
43 29 00 10	T10	2,7	100	116	14	5
43 29 00 15	T15	3,3	100	116	16	10
43 29 00 20	T20	3,8	100	125	36	10
43 29 00 25	T25	4,4	110	135	41	10
43 29 00 27	T27	5	110	135	49	10
43 29 00 30	T30	5,5	130	155	59	10
43 29 00 40	T40	6,6	130	165	102	10
43 29 00 45	T45	7,8	130	165	119	10
43 29 00 50	T50	8,8	130	165	137	5