


EBC139



Splitter box

ZDOAF03BMSS0000---STGH120MSS



Application	
Special feature	Gold-plated contacts
Electrical data	
Operating voltage	[V] 15...30 DC; ("supply class 2" to cULus)
Protection class	III
Max. current load per module/slot	[A] 2
Max. current load total	[A] 2
Outputs	
Electrical design	PNP

EBC139




Splitter box

ZDOAF03BMSS0000---STGH120MSS

Operating conditions		
Ambient temperature	[°C]	-25...80
Ambient temperature (moving)	[°C]	-5...60
Protection		IP 67; IP 68; (1 m / 7 days)
Mechanical data		
Weight	[g]	150.5
Materials		PBT-GF20; brass nickel-plated
Number of ports splitter box		10
Connector type		M8
Displays / operating elements		
Display	switching status	10 x LED, yellow
	operation	1 x LED, green
Accessories		
Accessories (optional)		Protective caps, for M8 sockets, E73005
Remarks		
Pack quantity		1 pcs.
Electrical connection - plug		


Connector: 1 x M12; Moulded body: PBT-GF 20 / brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.8...1.5 Nm



Splitter box

ZDOAF03BMSS0000---STGH120MSS

Connection



Electrical connection - socket

Connector: 1 x M8; Moulded body: PBT-GF 20 / brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.8...1.5 Nm

