



Model Number

PCV-USB-RS485-Converter Set

USB to RS 485 interface converter

Features

- Extension cable 0.8 m in scope of delivery
- Power supply for 95 - 230 V AC
- For RS485

Technical data

Indicators/operating means

Operation indicator	LED red
Data flow indicator	LED yellow and LED green

Electrical specifications

Operating voltage	U_B	via USB
-------------------	-------	---------

Interface 1

Connection of	PC
Interface type	USB

Interface 2

Connection of	Read head
Interface type	RS 422 / RS 485
Transfer rate	up to 921.6 kBit/s

Mechanical specifications

Connection type	Screw terminals for 0.14 ... 0.34 mm ² 9-pin Sub-D connector USB-Male Connector Typ B
Dimensions	70 mm x 67 mm x 22 mm

General information

Scope of delivery	USB connection cable 800 mm Software on CD-ROM 24 V power supply and V19 cordset USB/RS 485 converter
-------------------	---

Compliance with standards and directives

Standard conformity	
Standards	EN 60947-5-2:2007 IEC 60947-5-2:2007