



Article number		
LV short text		00100

Technical Data		
Operating current rated value	A	10
Operating voltage rated value maximum	V	230
Switching capacity active power	W	3 680
Switching capacity current	A	10
Number of switching outputs maximum		4
Suitability for use switching of C load		Yes
Suitability for operation Multiphase operation		Yes
Mounting type		modular installation device
Product extension can be installed supplementary devices		No
Product function direct operation		Yes
Number of width units		4
Protection class IP		IP20
Display version LED		No
Number of digital inputs		0
Bus coupling Integrated		Yes

## Certificates/approvals

<b>General Product Approval</b>	<b>Declaration of Conformity</b>	<b>other</b>
---------------------------------	----------------------------------	--------------

[Miscellaneous](#)



EG-Konf.

[Environmental Confirmations](#)

## Further information

**Gamma-TD (Tech. Documentation, ETS Product database, Invitation to tender text)**

<http://www.siemens.com/gamma-td?ssn=5WG1532-1DB31>

**Gamma - Catalogue**

<http://www.siemens.com/gamma-catalogue>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=5WG1532-1DB31&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=5WG1532-1DB31&lang=en)

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5WG1532-1DB31>

last modified:

08/08/2017